

# THE CLEAR FAMILY

## FEATURES

SITUATION	FEATURE	BENEFIT	CLEAR440	CLEAR330	CLEAR220
<b>Fitting</b>	Processing channels	For a more precise fitting	15	10	5
	Expanded Sensogram	Start the fitting process more accurately	14*	14*	14*
<b>Binaural hearing</b>	IE TruSound Compression	Find the voice in the crowd	●	-	-
	IE Speech Enhancer SII	Focus on the dominant voice in the crowd	●	-	-
<b>Feedback control</b>	IE Feedback Cancellation	Minimises whistling in all situations	●	●	●
<b>Sound localisation</b>	Digital Pinna	Helps you locate and focus naturally on the voice in front/behind	●	●	-
<b>Sound comfort</b>	TruSound Softener	Control undesirable transient sounds	●	●	-
	TruSound AOC	Ensures distortion-free sound performance	●	●	●
	Hammer detector	Detects and minimises undesirable loud sounds	●	●	●
<b>Speech understanding in noise</b>	HD Locator	For better hearing in noise	15 ch	10 ch	5 ch
	Speech Enhancer	For improved signal-to-noise ratio	IE	●	-
	Noise Reduction with SIS	Reduces noise and intensifies speech	●	●	●
<b>Sound relaxation</b>	IE Zen	Provides soothing tones and chimes in stereo	●	●	●**
<b>Tinnitus management</b>	IE Zen	For reducing the stress of tinnitus	●	●	●**
<b>Hearing high frequencies</b>	Audibility Extender	Enables hearing for high frequency dead regions	●	●	●
<b>Speech understanding in quiet</b>	TruSound Compression	Improve hearing for sounds of any loudness	IE	●	●
	EDRC	Hear soft sounds in the real world	●	●	●
	TruSound Stabilisers	Hear speech in changing listening situations	●	●	●
<b>Ease of use</b>	Phone+***	Hear phone calls in both hearing aids	●	●	-
	Reverse Focus program	Choose listening to speech from behind	●	●	●
	IE program shift	Change the program in both hearing aids together	●	●	●
	IE Partner Monitor	Keep the hearing aids coupled together	●	●	-
	Number of programs	More choice for the user	5	4	3
<b>Connectivity and control</b>	RC-DEX	For ease of use	●	●	●
	TV-DEX	For improved TV listening without echo or delay	●	●	●
	M-DEX	For better hearing on the mobile phone	●	●	●

● Indicates unique features in this class of hearing instrument. \*13 fitting bands in the 9-model. \*\*Optional. \*\*\*only available with Fusion and 9 models (choose between Phone+ and Zen+). IE = InterEar